

# Rittal – The System.

Faster – better – everywhere.



## SZ 2565.300 Plastic gland plate

State: 09.07.2026. (Source: [rittal.com/hr-hr](http://rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2565.300 - Plastic gland plate with membranes, for AX

Simply pierce the plastic with a sharp object, and pull through the cable.

## Features

|  |  |
|--|--|
| Model No.                                    | SZ 2565.300  |
| Product description                          | Simply pierce the plastic with a sharp object, and pull through the cable.   |
| Material                                     | Plastic to UL 94-V0  |
| Colour                                       | Similar to RAL 7035  |
| Note   | The allocation of gland plate sizes is indicated on the relevant enclosures  |
| Dimensions                                   | Width: 301 mm<br>Depth: 221 mm   |
| To fit                                       | Enclosure type: AX   |
| Gland plate                                  | Size: 5  |
| Protection category to IEC 60 529            | IP 66 if installed correctly   |
| Type rating to UL 50E                        | Type 1<br>Type 12  |
| No. of cable entries and Ø (mm)<br>min.-max. | 30 x 5-11<br>40 x 10-15<br>5 x 15-25<br>2 x 19-34<br>2 x 26-54<br>1 x 50-110 |
| Packs of                                     | 1 pc(s).   |
| Net weight                                   | 0,585 kg   |
| Gross weight                                 | 0,59 kg  |
| Customs tariff number                        | 39269097   |
| ETIM 9                                       | EC000211   |
| ETIM 8                                       | EC000211   |

# Features

---

|                     |  |
|---------------------|--|
| ECLASS 8.0          | 27142421   |
| Product description | SZ Plastic gland plates, for AX, with membranes, WD: 301x221 mm, for gland plates size 5 |

---

# Approvals

---

|           |                  |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|

---