
#### Rittal - The System.

Faster – better – everywhere.





# AX 2820.310 Base/plinth trim panels, side, 100 mm

State: 15.12.2025. (Source: rittal.com/hr-hr)



## AX 2820.310 - Base/plinth trim panels, side, 100 mm for AX

To finish off a base/plinth unit at the sides and for additional stabilisation or for the interior configuration of bayed base/plinths. One 200 mm high or two 100 mm high trim panels may optionally be fitted on 200 mm high base/plinths.

#### **Features**

Model No.	AX 2820.310	
Product description	To finish off a base/plinth unit at the sides and for additional stabilisation or for the interior configuration of bayed base/plinths.  One 200 mm high or two 100 mm high trim panels may optionally be fitted on 200 mm high base/plinths.	
Material	Sheet steel	
Colour	RAL 9005	
Supply includes	Assembly parts	
Note	Components from the 1st generation base/plinth system cannot be combined with components from the 2nd generation base/plinth system	
Dimensions	Height: 100 mm	
To fit	Enclosure type: AX Depth: = 300 mm	
Type rating to UL 50E	Type 1 Type 3R Type 4 Type 12	
Packs of	2 pc(s).	
Net weight	0.66	
Gross weight	0.667	
Customs tariff number	94039910	
EAN	4028177942554	

© Rittal 2025 2

#### Features

ETIM 9	EC000721	
ETIM 8	EC000721	
ECLASS 8.0	27182003	

### **Approvals**

Approvals UL + C-UL - FTTA

© Rittal 2025 3