Rittal - The System.

Faster - better - everywhere.






SV 3055.000 Busbar support

State: 17.11.2025. (Source: rittal.com/hr-hr)



SV 3055.000 - Busbar support

For busbar systems 1250 A (100 mm), 1600 A (185 mm), 2500 A (150 mm), 3000 A (150 mm).



Features

Model No.	SV 3055.000
Material	Fibreglass-reinforced, thermoplastic polyester (PBT) Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Number of poles	3-pole 150 mm
To fit busbars	60 x 10 80 x 10
Rated current max.	2.500 A
Dimensions	Width: 30 mm Height: 420 mm Depth: 160 mm
Packs of	2 pc(s).
Net weight	4.16
Gross weight	4.503
Customs tariff number	85469010
EAN	4028177035782
ETIM 9	EC001166
ETIM 8	EC001166

© Rittal 2025

Features

ECLASS 8.0

27400607

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK

Tender text

SV busbar support for accommodating busbars. Suitable for busbars up to 3 x 2 x 80 x 10 mm with inserts.

Rated operating voltage: 1000 V~, 50/60 Hz

to VDE 0660

Rated current: up to 2500 A

Material: PBT

Fire protection: UL 94-V0

Continuous operating temperature: 140 °C

Bar centre distance: 150 mm

Tightening torques

Assembly screw: 8 - 10 Nm Lid attachment: 5 - 10 Nm

© Rittal 2025

3