

# Rittal – The System.

Faster – better – everywhere.



## SK 3313.614 Connection hose

State: 13.05.2026. (Source: [rittal.com/hr-hr](http://rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3313.614 - Connection hose

Flexible connection hose, may be shortened, including union nuts on both sides for connecting the LCP/LCU to existing pipework.

## Features

|  |   |
|--|---|
| Model No.                                | SK 3313.614   |
| Design                                   | Rack cooling<br>CW  |
| Product description                      | The LCU cooling water connection is easily connected to the on-site pipework with the water connection kit. The hoses have a 90° bend on one side and a clamping tray on the other, to allow shortening of the hoses. Allows shortening of the hoses. |
| Material                                 | NBR (internal) with steel spiral and fabric inlay   |
| Length                                   | 2,5 m   |
| Water connections                        | G ¾" internal thread  |
| Operating temperature range              | -30 °C...70 °C  |
| Permissible operating pressure (p. max.) | 10 bar  |
| Packs of                                 | 2 pc(s).  |
| Net weight                               | 5,08 kg   |
| Gross weight                             | 5,485 kg  |
| Customs tariff number                    | 39173200  |
| ETIM 9                                   | EC002515  |
| ETIM 8                                   | EC002515  |
| ECLASS 8.0                               | 27180712  |
| Product description                      | SK Connection hose, for LCU CW 3313.610, length 2500 mm   |