

# Rittal – The System.

Faster – better – everywhere.



## SK 3321.705 Chopped-fibre filter mat

State: 29.06.2025. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3321.705 - Chopped-fibre filter mat

Spare filter mats for roof-mounted fans, fan-and-filter units or thermoelectric coolers, for effective protection of enclosure components from dirt, dust and water.

## Features

|                       |   |
|-----------------------|---|
| Model No.             | SK 3321.705   |
| Design                | for fan-and-filter units  |
| Product description   | Made of chopped-fibre mat with a progressive structure.<br>Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean-air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm. |
| Material              | Chemical fibres   |
| Note                  | Performance data, protection category and device approvals are only guaranteed when used in conjunction with original Rittal filter mats.   |
| To fit Model No.      | 3237.2xx/3237.1xx   |
| Dimensions            | Width: 89 mm<br>Height: 89 mm<br>Depth: 10 mm   |
| Filter class          | to DIN EN 779: G2<br>to DIN EN ISO 16890: ISO Coarse 50%  |
| Packs of              | 50 pc(s).   |
| Net weight            | 0.1   |
| Gross weight          | 0.156   |
| Customs tariff number | 56039390  |
| EAN                   | 4028177695535   |
| ETIM 9                | EC002513  |
| ETIM 8                | EC002513  |
| ECLASS 8.0            | 27180706  |

# Approvals

---

Certificates

EAC