## Rittal – The System.

Faster – better – everywhere.





# SK 3322.720 Pleated filter

State: 08.12.2025. (Source: rittal.com/hr-hr)



# SK 3322.720 - Pleated filter for fan-and-filter units, roof-mounted fans, cooling units and chillers

The high-quality pleated filter technology permits a significant increase in the volumetric air flow compared to conventional chopped-fibre filter mats. Cooling unit performance is improved and energy consumption is lower. The enhanced filtration properties also mean less dust in the enclosure or unit, and the resulting longer maintenance intervals reduce service costs significantly.



#### **Features**

Model No.	SK 3322.720
Design	for filter fans / outlet filters
Material	PET
Colour	White
Note	Performance data, protection category and device approvals are only guaranteed when used in conjunction with original Rittal filter mats.
To fit Model No.	3238.xxx
Dimensions	Width: 114 mm
	Height: 114 mm
	Depth: 14 mm
Filter class	to DIN EN 779: G4
	to DIN EN ISO 16890: ISO Coarse 70%
IP protection category to IEC 60 529	IP 54 in fan-and-filter units/roof-mounted fans/outlet filters
Note on Model No.	No suitable for use in EMC filter fans.

© Rittal 2025 2

### Features

Packs of	5 pc(s).
Net weight	0.095
Gross weight	0.1
Customs tariff number	56039390
EAN	4028177969162
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706

# Approvals

Approvals UR + C-UR (recognized)

© Rittal 2025 3