

Rittal – The System.

Faster – better – everywhere.



SK 3355.720

Electrical condensate evaporator

State: 13.05.2026. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3355.720 - Electrical condensate evaporator for Blue e+ roof-mounted cooling units

Condensate evaporation helps to evaporate any condensation and emit it to the ambient air via the air exhaust of the cooling unit.



Features

Model No.	SK 3355.720
Product description	Tool-free mounting of the condensate evaporator on the underside of the roof-mounted Blue e+ so that it is not visible from the outside. Any condensation is evaporated and emitted to the ambient air via the air exhaust of the cooling unit.
Material	Plastic
Colour	RAL 9005
Supply includes	Electrical condensate evaporator Shipping brace screw Entry grommet
Evaporation performance	100 ml/h
Note	Power is supplied via the cooling unit
To fit Model No.	3185.730 / 3485.730
Dimensions	Width: 89 mm Height: 121 mm Depth: 158 mm
Operating temperature range	5 °C...60 °C
Rated operating voltage	380 V (DC)
Packs of	1 pc(s).

Features

Net weight	0,4 kg
Gross weight	0,5 kg
Customs tariff number	84189910
ETIM 9	EC002009
ETIM 8	EC002009
ECLASS 8.0	27180715
Product description	SK Electrical condensate evaporation, for 3185.730/3485.730, plastic, WHD: 89 x 121x 158 mm