


Rittal – The System.

Faster – better – everywhere.



HD 4000.075

Fire extinguisher enclosure HD

State: 23.05.2026. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



HD 4000.075 - Fire extinguisher enclosure HD

Important security equipment is rapidly accessible and hygienically protected. The fire extinguisher housing may be sited directly in the production environment.

Features

Model No.	HD 4000.075
Product description	Roof angled forwards by 30°
Benefits	Hygienic, hose-proof storage of fire extinguishers Time and cost savings thanks to simple, effective cleaning options Fire extinguisher is easily removed with one hand thanks to the T handle Quick inventory check with the integral viewing door
Material	Enclosure and door: Stainless steel 1.4301 (AISI 304) Handle and lock: Stainless steel 1.4301 (AISI 304) Viewing window: Polycarbonate Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600
Surface finish	Enclosure and door: Brushed, grain 400, peak-to-valley height < 0.8 µm Seal: Blue, dyed (RAL 5010)
Supply includes	Enclosure of all-round solid construction Door with viewing window and inserted seal Interchangeable door hinge T handle with 3-point lock system
Dimensions	Width: 390 mm Height, front: 840 mm Height rear: 1,010 mm Depth: 300 mm
Visible area	Viewing window width: 170 mm Viewing window height: 670 mm
Packs of	1 pc(s).
Net weight	20 kg
Gross weight	22 kg

Features

PCF per pack (cradle-to-gate)	70.94
-------------------------------	-------

Customs tariff number	94032080
-----------------------	----------

ETIM 9	EC000261
--------	----------

ETIM 8	EC000261
--------	----------

ECLASS 8.0	27180101
------------	----------

Approvals

Explanations	PCF-declaration
--------------	-----------------