## Rittal – The System.

Faster – better – everywhere.





# AS 4051.100 Wire Station WS 540

State: 14.12.2025. (Source: rittal.com/hr-hr)



### AS 4051.100 - Wire Station WS 540

Mobile wiring workstation, height-adjustable, for flexible use in the workshop. For ergonomic, fatigue-free wire processing work.







#### **Features**

Model No.	AS 4051.100
Design	Standard
Product description	Mobile wiring workstation, height-adjustable, for flexible use in the workshop. For ergonomic, fatigue-free wire processing work.
Benefits	Electronically adjustable desk for the optimum working height, adjustable from 710 – 1250 mm  Multiplex worktop, washable and scratch-resistant Ideal solution in conjunction with the length-cutting and crimping machines plus pre-assembled wires with the Wire Terminal Integral scale for quick manual measurements  Prepared to accommodate a monitor for wire processing with Eplan Smart Wiring  Optionally expandable with shelves for wire boxes, wire reels and holders for tools and small parts  For flexible use in the workshop thanks to rubberised wheels  Drawer with shadow board prepared for tools
Supply includes	Wiring table with electrical height adjuster Connection cable, 7 m 7-way socket strip, with rocker switch
Assembly instruction	The vertical mounting struts, Model No. 4051.106, are required for accessories such as storage box holders, magazine supports etc.
Input voltage	230 V AC, 50 Hz

© Rittal 2025

## **Features**

Dimensions	Width: 900 mm
	Height: 1,350 mm
	Depth: 781 mm
Working height	Working height (min.): 710 mm
	Working height (max.): 1,205 mm
Height adjustable y/n	Yes
Packs of	1 pc(s).
Net weight	95
Gross weight	107
Customs tariff number	94032080
EAN	4028177957480
ETIM 9	EC002224
ETIM 8	EC002224
ECLASS 8.0	21100204

# Approvals

Explanations	Declaration of conformity
--------------	---------------------------

© Rittal 2025 3