

Rittal – The System.

Faster – better – everywhere.



AS 4051.603 Wire end ferrules

State: 24.06.2026. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.603 - Wire end ferrules on a reel

With plastic collar.

Features

Model No.	AS 4051.603
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	Red
Length	8 mm
AWG	16
Internal diameter	3,5 mm
Rittal colour code	Yes
For cross-section	1,5 mm ²
Note	UL-certified in conjunction with the relevant tools, such as crimping machines.
Standards	AEH DIN 46228
Delivery form	Taped
Packs of	5.000 pc(s).
Net weight	5 kg
Gross weight	0,729 kg
Customs tariff number	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

Features

Product description	Wire end ferrules for crimping machines, 1.5 mm ² , AWG 16, 8 mm, red, on belt, 5000 pc(s).
---------------------	--------------------------------------------------------------------------------------------------------

Approvals

Approvals	UL + C-UL (listed) UR
-----------	--------------------------