

# Rittal – The System.

Faster – better – everywhere.



## AS 4051.684 Wire end ferrules

State: 09.04.2026. (Source: [rittal.com/hr-hr](http://rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4051.684 - Wire end ferrules loose

With plastic collar.

## Features

|                          |   |
|--------------------------|---|
| Model No.                | AS 4051.684   |
| Product description      | With plastic collar.  |
| Technical specifications | Heat-resistant to 105 °C  |
| Material                 | E-Cu, galvanic tin-plated<br>Plastic collar: Polypropylene  |
| Colour                   | Grey  |
| Length                   | 10 mm   |
| AWG                      | 18  |
| Internal diameter        | 3,4 mm  |
| DIN colour code          | Yes   |
| Multinorm                | Yes   |
| Note                     | UL-certified in conjunction with the relevant tools, such as crimping machines.<br>For bespoke advice, please contact your Rittal sales consultant. |
| Delivery form            | Loose   |
| Packs of                 | 500 pc(s).  |
| Net weight               | 0,5   |
| Customs tariff number    | 85369010  |
| ETIM 9                   | EC000005  |
| ETIM 8                   | EC000005  |
| ECLASS 8.0               | 36659290  |
| Product description      | Wire end ferrules for wire processing 0.75 mm <sup>2</sup> , grey, loose, 10 mm   |

# Approvals

---

Approvals

UL + C-UL (listed)

UR