

Rittal – The System.

Faster – better – everywhere.



AS 4052.122 Screwdrivers

State: 23.06.2025. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4052.122 - Screwdrivers insulated

With a long, slender handle and high-performance tip with non-transfer insulation.

Features

Model No.	AS 4052.122
Design	Isolation protection 1000 V for Pozidriv screws
Product description	With a long, slender handle and high-performance tip with non-transfer insulation.
Benefits	Minimal force required, thanks to ergonomically styled handle Handle head with anti-roll protection and clear screw labelling Black coated blade tip to preserve precision and accuracy of fit Handle 30% and insulation up to 50% slimmer than comparable tools Optimum interconnection of hand and handle supports higher torques and longer, fatigue-free working
Material	Blade: Chrome-molybdenum-vanadium alloy Handle core: Hard plastic Handle body: Elastic, highly flexible plastic
Colour	Handle: Anthracite and Rittal Power Pink
Blade dia.	6 mm
Blade length	100 mm
Blade tip	PZ 2
Handle dia.	27 mm
Handle length	115 mm
Standards	IEC 60 900
Packs of	1 pc(s).
Net weight	0.07
Gross weight	0.077
Customs tariff number	82054000

Features

EAN	4028177807266
ETIM 9	EC000144
ETIM 8	EC000144
ECLASS 8.0	21040406