

# Rittal – The System.

Faster – better – everywhere.



## AS 4054.140 Crimping pliers

State: 11.07.2025. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4054.140 - Crimping pliers for ring terminals

For use with insulated ring terminals and connectors



## Features

Model No.	AS 4054.140
Design	Angled
Product description	For use with insulated ring terminals and connectors.
Benefits	Clear allocation of cross-sections, thanks to colour coding on the dies Releasable ratchet Releases as soon as the required pressure is reached, to prevent underpressing
Material	High-quality special tool steel
Surface finish	Matt, plated
Colour	Handle: Anthracite and Rittal Power Pink
Compression	Oval crimp
Dimensions	Height: 59 mm Length: 198 mm
AWG	22 - 14
For cross-section	0.75 - 2.5 mm <sup>2</sup>
Packs of	1 pc(s).
Net weight	0.42
Gross weight	0.44

# Features

Customs tariff number	82032000
EAN	4028177807686
ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811