


Rittal – The System.

Faster – better – everywhere.



AS 4055.720 Electro-hydraulic pump

State: 30.05.2026. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.720 - Electro-hydraulic pump

The electro-hydraulic pump is used to drive products in the CW 120-S series.



Features

Model No.	AS 4055.720
Product description	The electro-hydraulic pump is used to drive products in the CW 120-S product series.
Power consumption	1,3 kW
Filling volume	3,2 l
Working volume	2,2 l
Flow rate (max.)	1,1 l/min
Oil (type)	HLP 46
Rated operating voltage	230 V, 50 Hz
Rated current	5,65 A
Machine dimensions	Width: 400 mm Height: 325 mm Depth: 335 mm
Support area	Width: 402 mm Height: 342 mm Depth: 397 mm
Permissible operating pressure (p. max.)	700 bar
Packs of	1 pc(s).
Net weight	32 kg

Features

Gross weight	34,5 kg
Customs tariff number	84138100
ETIM 9	EC011047
ETIM 8	EC011047
ECLASS 8.0	27301290
Product description	Electro-hydraulic pump suitable for CW 120 – S and hydraulic cylinders

Approvals

Explanations	Declaration of conformity
--------------	---------------------------