Rittal – The System.

Faster – better – everywhere.





SZ 4139.300 Courtesy light

State: 22.11.2025. (Source: rittal.com/hr-hr)



SZ 4139.300 - Courtesy light

Supply voltage: 100 - 240 V AC 50/60 Hz

Features

| Model No. | SZ 4139.300 |
|---|--|
| Design | without door operated switch |
| Supply includes | Courtesy light |
| | Light |
| | Light cover |
| | Assembly parts |
| Power consumption | 30 W |
| Ballast | Wide-range electronic ballast |
| Connection options | Power supply via connectors |
| | Door-operated switch |
| | Through-wiring (creating rows of lights) |
| Light | Fluorescent lamp, base G13 |
| Protection class | I (PE conductor) |
| Switch (type) | Integral on/off/door-operated switch |
| Light cover | Yes |
| Light – installation type | Screw-fastening |
| Rated impulse withstand voltage, phase to earth | 2000 V AC |
| Rated impulse withstand voltage, phase to phase | 1000 V AC |
| Rated insulation voltage | 500 V DC/1s |
| | |

© Rittal 2025

Features

| Installation options | TS horizontal section of the roof frame: direct |
|-----------------------------|--|
| | TS, SE vertical section: with TS adaptor bracket |
| | SE sections at the front and rear of the roof frame: with TS adaptor |
| | bracket |
| | SE extrusions at the side of the roof frame: direct |
| | AE, CM, TP: with universal bracket |
| | AE: with rail for interior installation |
| Dimensions | Width: 987 mm |
| | Height: 117 mm |
| | Depth: 50 mm |
| Operating temperature range | -15 °C45 °C |
| Sockets | D, earthing-pin (type F, CEE 7/4) |
| Storage temperature range | -20 °C70 °C |
| Rated operating voltage | 100 V - 240 V, 1~, 50 Hz/60 Hz |
| Socket version | D, earthing-pin (type F, CEE 7/4) |
| Packs of | 1 pc(s). |
| Net weight | 2.15 |
| Gross weight | 2.3 |
| Customs tariff number | 94054990 |
| EAN | 4028177092365 |
| ECLASS 8.0 | 27189241 |
| | |

Approvals

| Explanations | Declaration of conformity |
|--------------|------------------------------|
| | Declaration of conformity UK |

© Rittal 2025 3