

Rittal – The System.

Faster – better – everywhere.



PS 4179.000

U nut

State: 23.05.2026. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PS 4179.000 - U nut

For mounting punched rails and punched sections without mounting flanges on angle brackets, mounting brackets and support brackets.



Features

Model No.	PS 4179.000
Installation options	Punched rail 23 x 23 mm Punched section without mounting flange, 23 x 73 mm Punched section without mounting flange, 45 x 88 mm Punched section with mounting flange, 23 x 73 mm
Note	For mounting punched rails and punched sections without mounting flanges on angle brackets, mounting brackets and support brackets, we recommend U nuts with M6 thread
Dimensions	Thread: M6
Thread	M6
Packs of	20 pc(s).
Net weight	0,34 kg
Gross weight	0,378 kg
Customs tariff number	73181692
ETIM 9	EC000096
ETIM 8	EC000096
ECLASS 8.0	23110804
Product description	SZ U nut, for thread M6