
Rittal – The System.

Faster – better – everywhere.





SZ 4947.000 C rails 30/15

State: 27.10.2025. (Source: rittal.com/hr-hr)



SZ 4947.000 - C rails 30/15 to EN 60 715 for VX, TS, VX SE

For direct external mounting on the horizontal enclosure section or vertical enclosure section with additional assembly components.





Features

SZ 4947.000
Sheet steel
Zinc-plated
1.155 mm
On the inner mounting level of the VX enclosure section On the vertical TS, VX SE enclosure section via snap-on nuts TS 8800.808 or adaptor rails for VX compatibility On the horizontal VX SE enclosure section in the width, top and bottom On the horizontal VX SE enclosure section in the depth at the bottom (without mounting plate) and at the top via snap-on nuts 8800.808. On the horizontal TS enclosure section In the width or depth of the 3-part AX. Depending on the installation situation, the bar will need to be shortened to the required size.
In base/plinth width 1200 mm on the base/plinth trim panels, in conjunction with holder/spacer
In base/plinth width 1200 mm, in conjunction with metal multi-tooth screws

© Rittal 2025

Features

To fit	Enclosure type: VX
	TS
	AX wall-mounted enclosure, 3-part
	To fit width/depth: 1,200 mm
To fit	Base/plinth system AX
	Base/plinth system VX
Packs of	6 pc(s).
Net weight	4.68
Gross weight	4.86
PCF per pack (cradle-to-gate)	19 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
EAN	4028177114654
ETIM 9	EC000386
ETIM 8	EC000386
ECLASS 8.0	27400602

© Rittal 2025 3