

Rittal – The System.

Faster – better – everywhere.



VX 5301.333

**Gland plate module, one-piece, with
brush strip**

State: 23.05.2026. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5301.333 - Gland plate module, one-piece, with brush strip for VX IT

For targeted cable entry from below.

Features

| | |
|-------------------------------|---|
| Model No. | VX 5301.333 |
| Design | one-piece, with brush strip |
| Product description | For targeted cable entry from below. |
| Material | Module plate: Sheet steel Brush strip: Plastic, UL 94 HB, halogen-free Module plate: Sheet steel Brush strip: Plastic, UL 94 HB, halogen-free |
| Surface finish | Module plate: Zinc-plated |
| Supply includes | Assembly parts |
| Assembly instruction | Several gland module plates must be combined to seal the base completely in the VX IT The gland plate module may be combined in exchange with other base modules with a depth of 237.5 mm. |
| Note | Gland plate modules with brush strip not suitable for applications with a protection category to IEC 60 529 |
| Dimensions | Depth: 237.5 mm |
| To fit | Enclosure type: VX IT Width: = 800 mm |
| Packs of | 1 pc(s). |
| Net weight | 1,82 kg |
| Gross weight | 2,06 kg |
| PCF per pack (cradle-to-gate) | 7.7 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |

Features

| | |
|-----------------------|---|
| Customs tariff number | 94039910 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |
| Product description | VX IT gland plate module with brush strip, for width 800 mm, W x D 600 x 237.5 mm, one-piece, sheet steel |

Tender text

VX IT Gland plate module, Art.-No. 5301.332,
with brush strip, for cable routing
For a rack width of 800 mm
Depth: 237,5 mm
For VX, VX IT
For a cable entry over brushes
Module plate: Sheet steel, zinc-plated
Brush strip: UL 94-HB, halogen-free