

Rittal – The System.

Faster – better – everywhere.



DK 5501.400

Slide rail, 2 U, static installation

State: 30.01.2026. (Source: rittal.com/hr-hr)

DK 5501.400 - Slide rail, 2 U, static installation for VX IT

For mounting between 482.6 mm (19") mounting angles.

Features

Model No.	DK 5501.400
Product description	System punchings for mounting accessories and cooling active components.
Applications	For mounting on a 482.6 mm (19") mounting level
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Length	150 mm
Installation options	for 482.6 mm (19") mounting angles, standard for 482.6 mm (19") mounting angles, dynamic
Load capacity	300 N, static
Packs of	2 pc(s).
Net weight	0.62
Gross weight	0.703
PCF per pack (cradle-to-gate)	2.6 kg CO ₂ eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
EAN	4028177678958
E-Number Sweden	E7239598
ETIM 9	EC002620
ECLASS 8.0	27189261