

Rittal – The System.

Faster – better – everywhere.



CX 6713.000 CX desk unit

State: 03.04.2026. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CX 6713.000 - CX desk unit

Four widths form the bridge to two- or three-piece assembly of the CX console system.



Features

Model No.	CX 6713.000
Design	Desk section
Material	Enclosure: Sheet steel 1.5 mm Console lid: Sheet steel 2.0 mm, all-round foamed-in PU seal
Surface finish	Enclosure and cover: Dipcoat primed, powder-coated on the outside, textured paint
Colour	RAL 7035
Supply includes	Enclosure Cover hinged at rear, 2 stays with automatic locking. Automatic unlocking on the left, manual unlocking on the right Opening for running cables into the enclosure base Lock: 3 mm double-bit Enclosure Cover hinged at bottom, including cover retainer Open base for individual cable entry
Dimensions	Width: 1,600 mm Depth: 745 mm
Height, front	130 mm
Height rear	200 mm

Features

IK Code	IK10
Note	A cover plate is required to seal the desk unit A pedestal and a cover plate for desk unit are required for 2-part console assembly. A pedestal and desk unit are required for a 3-part console assembly.
IP protection category to IEC 60529	IP 55
Protection category NEMA	NEMA 1 NEMA 12
Basic material	Sheet steel
Dimensions	Width: 1,600 mm
Number of locks	3
Lock version	Cam
Lock insert	3 mm double-bit
Lock	Lock version: Cam Number of locks: 3 Lock insert: 3 mm double-bit
Packs of	1 pc(s).
Net weight	46 kg
Gross weight	47 kg
Customs tariff number	94032080
ETIM 9	EC000784
ETIM 8	EC000784
ECLASS 8.0	27180504
Product description	CX console system, desk unit, W: 1600 mm

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------

Approvals

Explanations

Declaration of conformity