

Rittal – The System.

Faster – better – everywhere.



DK 7111.300 Snap-in cable routing

State: 27.05.2026. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

DK 7111.300 - Snap-in cable routing

For fast, tool-free assembly in two variants: snap-mounting and twist-mounting.



Features

Model No.	DK 7111.300
Design	for snap-mounting
Benefits	The diameter of the cable routing clip may be adapted to the routed cable cross-section
Material	Polyamide 6.6, self-extinguishing to UL 94-V2
Colour	Natural
Cable entry	Min. cable diameter: 14 mm Max. cable diameter: 19 mm
For system punchings with Ø	6,2 mm
Min. cable diameter	14 mm
Max. cable diameter	19 mm
Packs of	10 pc(s).
Net weight	0,03 kg
Gross weight	0,043 kg

Features

Customs tariff number	39269097
ETIM 9	EC002625
ECLASS 8.0	27189234
Product description	DK snap-in cable routing for snap-mounting, for fast, tool-free assembly, for max. Ø 19 mm, polyamide, natural