

# Rittal – The System.

Faster – better – everywhere.



## DK 7163.565 Cable support

State: 03.06.2026. (Source: [rittal.com/hr-hr](http://rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7163.565 - Cable support hinged, with anti-kink device and clamp

Kink-free cable routing in the central part via mobile chain links, the attachment may be released on both sides, thanks to clamps.



## Features

Model No.	DK 7163.565
Product description	For secure routing of connection cables from the component shelf to the clamping point. Kink-free cable routing in the central part via mobile chain links. The attachment may be released on both sides thanks to clamps.
Material	Sheet steel, zinc-plated Centre part: Plastic
Supply includes	Assembly parts
Note	Max. depth of component shelves = Enclosure depth - 200 mm.
To fit	Depth: > 600 mm
Packs of	1 pc(s).
Net weight	0,7 kg
Gross weight	0,78 kg
PCF per pack (cradle-to-gate)	2.8 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098

# Features

---

ETIM 9	EC000322
--------	----------

---

ECLASS 8.0	27400604
------------	----------

---

Product description	DK Cable support, kink-free, For D: > 600 mm, Max. depth component shelf = depth rack-200 mm
---------------------	--

## Tender text

Kink-free cable support  
for enclosures larger than 600 mm  
Material: Sheet steel, zinc-plated, passivated