

# Rittal – The System.

Faster – better – everywhere.



## DK 7320.435 CMC III power pack

State: 03.08.2025. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7320.435 - CMC III power pack for PU, PU Compact, LED light strip, door control module

CMC III power pack for use across multiple voltage ranges.



## Features

|                       |   |
|-----------------------|---|
| Model No.             | DK 7320.435   |
| Product description   | The power pack is specifically tailored to the CMC III design and may be positioned in a mounting unit. As well as a special connector for the CMC III Processing Unit/Compact, there are also two further terminals available as 24 V outputs. |
| Output current (max.) | 1,3 A   |
| Suitable for CMC      | CMC III Processing Unit<br>CMC III Processing Unit Compact  |
| Dimensions            | Width: 138 mm<br>Height: 40 mm<br>Depth: 144 mm   |
| Output voltage        | Output voltage: 24 V DC   |
| Packs of              | 1 pc(s).  |
| Net weight            | 0.52  |
| Gross weight          | 0.605   |
| Customs tariff number | 85043121  |
| EAN                   | 4028177367333   |

# Features

---

|            |          |
|------------|----------|
| ETIM 9     | EC002627 |
| ECLASS 8.0 | 27189253 |

---

# Approvals

---

|              |                           |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|

---

# Tender text

Power pack 48 V DC / 24 V DC for PU

This 48 V DC power pack is required to supply the processing unit II with power. It requires an IEC connection cable to supply the voltage.

Primary range: 48 V DC, via terminal block  
Secondary range: 24 Volt DC, 0,6 A;  
Output cable 1.65 m

Fastening with top hat rail ( EN 50022 )

Packs of 1.