


Rittal – The System.

Faster – better – everywhere.



DK 7401.000

Depth stays

State: 10.08.2025. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7401.000 - Depth stays for Data Rack

For securing and stabilising two pairs of 482.6 mm (19") mounting angles in the Data Rack, the length is adjustable.

Features

Model No.	DK 7401.000
Product description	For securing and stabilising two pairs of 482.6 mm (19") mounting angles in the Data Rack. The length of the depth stays is adjustable, and can accommodate the following spacings of mounting angles: 250, 300 and 350 mm.
Material	Sheet steel
Surface finish	Spray-finished
Colour	RAL 7035
Supply includes	Assembly parts
Installation dimensions	Installation depth for components: 482.6 mm Installation width for components: 19"
Packs of	2 pc(s).
Net weight	0.76
Gross weight	0.906
PCF per pack (cradle-to-gate)	3.5 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
EAN	4028177129993
E-Number Sweden	E7282524
ETIM 9	EC002620
ECLASS 8.0	27189261

Tender text

Depth stays

For securing and stabilising two pairs of 482.6 mm (19") mounting levels in the data rack. The length of the depth stay can be adjusted and it enables a 50 mm pitch pattern to be set up for the mounting angles.

Material: Sheet steel

Surface finish: RAL 7035