

# Rittal – The System.

Faster – better – everywhere.



## TE 7526.834 Module plates

State: 05.06.2026. (Source: [rittal.com/hr-hr](http://rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TE 7526.834 - Module plates for TE

The base area of the TE may be varied as required using the module plates.

## Features

Model No.	TE 7526.834
Design	Vented
Product description	The base area of the TE may be varied as required using the module plates.
Applications	Please note when selecting suitable gland plates: Enclosure width minus 150 mm Enclosure depth minus 50 mm
Material	Sheet steel, zinc-plated
Supply includes	Assembly parts
Dimensions	Width: 650 mm Depth: 200 mm
To fit	Enclosure type: TE Width: 800 mm
Packs of	1 pc(s).
Net weight	0,82 kg
Gross weight	1,02 kg
Customs tariff number	94039910
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	TE Module plate, WxD: 650x200 mm, Vented, For W: 800 mm

# Tender text

Vented module plate

650 mm wide module plate, 200 mm deep module plate

Material: Sheet steel, zinc-plated