

# Rittal – The System.

Faster – better – everywhere.



## DK 7688.000

## 482.6 mm (19") mounting angles

State: 23.05.2026. (Source: [rittal.com/hr-hr](http://rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7688.000 - 482.6 mm (19") mounting angles for DK PS, CS New Basicgehäuse

For mounting 482.6 mm (19") components in Networking and Server Racks DK PS and in Outdoor enclosures CS New Basic

## Features

Model No.	DK 7688.000
Product description	For mounting 482.6 mm (19") components in DK PS network and server enclosures and in CS New Basic outdoor enclosures. The mounting angles are depth-adjustable on a 25 mm pitch pattern. A depth stay is required to attach the mounting angles.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Units	24 U
Installation dimensions	Installation depth for components: 482.6 mm Installation width for components: 19"
To fit	Enclosure type: CS basic enclosures DK PS Height: = 1,200 mm
Packs of	2 pc(s).
Net weight	2,494 kg
Gross weight	2,693 kg
PCF per pack (cradle-to-gate)	10.3 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261

# Features

---

Product description

DK 482.6 mm (19") mounting angles, 24 U, For H: 1200 mm