


Rittal – The System.

Faster – better – everywhere.



DK 7824.202

Glazed door, vented

State: 09.05.2025. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7824.202 - Glazed door, vented for TS, TS IT, VX SE

To replace existing doors. With 180° hinges and swivel handle with security lock no. 3524 E.

Features

Model No.	DK 7824.202
Product description	Surface perforated on both sides with air inlet openings > 78% for optimum air throughput.
Material	Door: Sheet steel Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Colour	RAL 7035
Supply includes	Glazed door, vented Comfort handle for profile half-cylinders with security lock 3524 E 180° hinges (4) Assembly parts
Assembly instruction	For TS enclosure suites with sheet steel doors, only the 180° hinge 7824.520 may be used.
To fit	Enclosure type: TS TS IT SE Width: 800 mm Height: 2,000 mm
Packs of	1 pc(s).
Net weight	24.89
Gross weight	26.2
Customs tariff number	94039910
EAN	4028177236127
ETIM 9	EC000747
ECLASS 8.0	27182204

Tender text

Material

Sheet steel, spray-finished

Colour

RAL 7035

Dimensions mm W x H x D

800 x 2000

Lock system

Comfort handle including security insert (no. 3524 E.)