


# Rittal – The System.

Faster – better – everywhere.



## DK 7824.280

## Sheet steel glazed door, vertically divided

State: 16.05.2024. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7824.280 - Sheet steel glazed door, vertically divided for TS 8

To replace existing doors. Thanks to the minimal rotation radius of the individual doors, the distance between individual bayed enclosure suites may be reduced.

## Features

Model No.	DK 7824.280
Product description	With underlaid viewing panel, 4-point locking rod and comfort handle for profile half-cylinders with security lock 3524 E. The divided design allows room-optimised siting of the enclosures coupled with the best possible access, thanks to a reduced distance between the individual bayed enclosure suites. Max. door opening angle thanks to pre-integrated 180° hinges.
Material	Frame: Sheet steel Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Colour	RAL 7035
Supply includes	Assembly parts
Note	Height 2200 mm cannot be combined with swing frame 45 U.
IP protection category to IEC 60529	IP 55
To fit	Enclosure type: TS 8 Width: 800 mm Height: 2,000 mm
Packs of	1 pc(s).
Weight/pack	35,4 kg
EAN	4028177570924
ETIM 7.0	EC000747
ECLASS 8.0	27182204

# Tender text

Sheet steel glazed door, vertically divided for TS  
With underlaid viewing panel, 4-point locking rod  
and comfort handle for semi-cylinder with security  
lock 3524 E. Max. door opening angle 180°.

Material:

Sheet steel, viewing window toughened safety  
glass, 4 mm

Colour: RAL 7035

For enclosures (W x H): 800 x 2000 mm