


Rittal – The System.

Faster – better – everywhere.



DK 7859.081

PSM Zero-U-Space


State: 20.01.2026. (Source: rittal.com/hr-hr)



FRIEDHELM LOH GROUP

DK 7859.081 - PSM Zero-U-Space

Modular PDU for space-saving integration in the zero-U space between side panel and 482.6 mm (19") mounting level in 800 mm wide IT racks.



Features

Model No.	DK 7859.081
Product description	Modular PDU for space-saving integration in the zero-U space between side panel and 482.6 mm (19") mounting level in 800 mm wide IT racks.
Material	Aluminium section, natural anodised
Length	1.695 mm
Length of connection cable	3 m
Type of electrical connection	fixed/CEE
Qty.	1
Phases per infeed	3~
Rated current (max.)	16 A
Module slots (max.)	6
IP protection category to IEC 60 529	IP 20
Dimensions	Length: 1,695 mm

Features

To fit	Enclosure type: VX IT Height: \geq 2,000 mm
Operating temperature range	5 °C...45 °C
Ambient humidity (non-condensing)	10...90 %
Packs of	1 pc(s).
Net weight	4
Gross weight	4.3
Customs tariff number	85369001
EAN	4028177956636
ETIM 9	EC002762
ECLASS 8.0	27371306

Approvals

Explanations	Declaration of conformity
--------------	---------------------------
