

Rittal – The System.

Faster – better – everywhere.



TS 8614.840 Partial mounting plates

State: 09.09.2025. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8614.840 - Partial mounting plates for TS, VX SE

For universal interior installation and additional mounting levels.



Features

| | |
|---------------------|--|
| Model No. | TS 8614.840 |
| Product description | For universal interior installation, also in conjunction with punched sections with mounting flanges and support strips. Defective assemblies are quickly and easily replaced. Additional mounting levels. |
| Material | Sheet steel, 2.5 mm |
| Surface finish | Zinc-plated |
| Supply includes | Assembly parts |
| Note | Partial mounting plates are fastened directly onto the vertical enclosure sections via the inner mounting level using the assembly parts supplied loose. In this mounting position (in both the width and the depth) they form one level with TS punched sections with mounting flanges 17 x 73 mm and TS support strips for the inner mounting level. |
| Dimensions | Width: 700 mm Height: 300 mm |

Features

| | |
|-----------------------|---|
| To fit | Enclosure type: TS VX SE Width: = 400 mm = 800 mm Depth: = 400 mm = 800 mm |
| Packs of | 1 pc(s). |
| Net weight | 5.176 |
| Gross weight | 5.448 |
| Customs tariff number | 94039910 |
| EAN | 4028177212343 |
| ETIM 9 | EC000213 |
| ECLASS 8.0 | 27409216 |