



# VX 8617.501 - Baying block, internal for VX, VX IT

Supports flexible positioning and all-round mounting at the baying point. Side mounting creates a flush surface, suitable for top mounting.

## Features

Model No.	VX 8617.501
Benefits	Side mounting creates a flush surface to the extrusion, suitable for top mounting, thus avoiding collisions with installed equipment For all-round installation on the baying joint
Material	Die-cast zinc
Supply includes	Baying block, internal Baying seal Assembly parts
Note	For baying enclosures with a width/depth > 800 mm, 2 packs are required for installation
To fit	Enclosure type: VX VX IT
Type rating to UL 50E	Type 1 Type 3R Type 4 Type 4X Type 12
IP protection category to IEC 60 529	IP 55
Packs of	6 pc(s).
Net weight	0.822
Gross weight	0.86
Customs tariff number	76169990
EAN	4028177919334
E-Number Sweden	E3465118
ETIM 9	EC002622

# Features

---

ECLASS 8.0

27189263

# Approvals

---

Approvals

UL + C-UL - FTTA