
### Rittal - The System.

Faster - better - everywhere.





# VX 8618.010 Glazed door

State: 14.12.2025. (Source: rittal.com/hr-hr)



### VX 8618.010 - Glazed door for VX

Instead of a sheet steel door or rear panel.

#### **Features**

Model No.	VX 8618.010
Product description	Instead of a sheet steel door or rear panel.
Material	Frame: Extruded aluminium section Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Colour	Frame: RAL 7035 Viewing window (printed mask on the inside): RAL 9005
Supply includes	Glazed door Locking rod with double-bit insert 180° hinges (4)
IK Code	IK08
Note	Lock components for frame 8618.110 are required when mounting instead of the rear panel
Type rating to UL 50E	Type 1 Type 12
IP protection category to IEC 60 529	IP 55
To fit	Enclosure type: VX Width: = 800 mm Height: = 1,800 mm
Packs of	1 pc(s).
Net weight	15.2
Gross weight	16
EAN	4028177920972
ETIM 9	EC000747
ECLASS 8.0	27182204

© Rittal 2025

## Approvals

Approvals	UL + C-UL - FTTA
Certificates	Protection category

© Rittal 2025 3