

# Rittal – The System.

Faster – better – everywhere.



## VX 8619.470 Bracket/spacer

State: 06.09.2025. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8619.470 - Bracket/spacer for base/plinth system VX, sheet steel

For flexible attachment of C rails or cable clamp rails. For installation in the VX base/plinth or on the enclosure frame section.



## Features

Model No.	VX 8619.470
Material	Die-cast zinc
Supply includes	2 support / spacer brackets Assembly parts
To fit	Enclosure type: VX TS VX SE
Weight/pack	0,298 kg
Packs of	2 pc(s).
Installation options	On the horizontal and vertical VX enclosure section On the punched sections with mounting flanges for the inner mounting level On the vertical TS, VX SE enclosure section via snap-on nuts TS 8800.806 or adaptor rails for VX compatibility On the horizontal TS enclosure section On the horizontal VX SE enclosure section, bottom On the horizontal VX SE enclosure section, top in the depth On enclosures and rails with rectangular system punching 12.5 x 11 mm On base/plinth corner piece with base/plinth trim, front and rear On base/plinth trim panels, side

# Features

For threads	M8
To fit	for base/plinth system VX, sheet steel
Assembly instruction	In VX SE, on the enclosure section in conjunction with VX adaptor rail M8 x 16 cheese-head screws and washers are required to attach a C-rail
Net weight	0.28
Gross weight	0.289
Customs tariff number	73269098
EAN	4028177984820
ETIM 9	EC002620
ETIM 8	EC000721
ECLASS 8.0	27182003