Rittal – The System.

Faster – better – everywhere.





VX 8640.040 Base/plinth trim panels, side, 200 mm

State: 11.11.2025. (Source: rittal.com/hr-hr)



VX 8640.040 - Base/plinth trim panels, side, 200 mm for base/plinth system VX, sheet steel

To finish off a base/plinth unit at the sides and for additional stability or interior configuration of bayed base/plinths. One 200 mm high or two 100 mm high trim panels may optionally be fitted on 200 mm high base/plinths.

Features

Model No.	VX 8640.040
Product description	To finish off a base/plinth unit at the sides and for additional stabilisation or for the interior configuration of bayed base/plinths. One 200 mm high or two 100 mm high trim panels may optionally be fitted on 200 mm high base/plinths.
Material	Sheet steel
Colour	RAL 9005
Supply includes	Assembly parts
Dimensions	Height: 200 mm
To fit	Depth: = 300 mm
Type rating to UL 50E	Type 1 Type 12
Weight/pack	1,12 kg
Packs of	2 pc(s).
Net weight	1.1
Gross weight	1.124
Customs tariff number	94039910
EAN	4028177959019
E-Number Sweden	E3465383
ETIM 9	EC000721
ECLASS 8.0	27182003

© Rittal 2025 2

Approvals

Approvals

UL + C-UL - FTTA

© Rittal 2025 3