

Rittal – The System.

Faster – better – everywhere.



SV 9340.560 OM adaptors

State: 03.02.2026. (Source: rittal.com/hr-hr)



SV 9340.560 - OM adaptors with spring terminals



Features

Model No.	SV 9340.560
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 7035
Rated current max.	32 A
Rated operating voltage	690 V, 3~
For bar systems with centre-to-centre spacing	60 mm
Support rail type	Support frame, 1 x TS 45D, 1 x TS 45D-V
Number of poles	3-pole
Support frame support	Yes
Dimensions	Width: 45 mm Height: 272 mm
Connection of round conductors	1.5 - 6 mm ²
Support rails Qty/height	2 / 10 mm
To fit busbars	Height: 5, 10 mm
Support frame (W x H)	45 mm x 237 mm
Packs of	1 pc(s).
Net weight	0.28

Features

Gross weight	0.293
Copper weight (kg per piece)	0.027
Customs tariff number	85369095
EAN	4028177664234
ETIM 9	EC001531
ECLASS 8.0	27370304

Approvals

Approvals	ABS DNV-GL Lloyds Register of Shipping
Explanations	Declaration of conformity Declaration of conformity UK