

Rittal – The System.

Faster – better – everywhere.



PK 9514.050

Polycarbonate enclosures PK

State: 12.05.2026. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PK 9514.050 - Polycarbonate enclosures PK with knockouts

Wall-mounted enclosure of fibreglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



Features

Model No.	PK 9514.050
Design	PK enclosure with solid cover
Material	Enclosure: Fibreglass-reinforced polycarbonate Cover: Fibreglass-reinforced polycarbonate, all-round foamed-in PU seal Cover screws: Polyamide Insulating bungs: Polyethylene
Colour	RAL 7035
Supply includes	Enclosure with cover Cover screws Insulating bungs for wall mounting screws
Protection category NEMA	NEMA 4X
Protection category to IEC 60 529	IP 66
IK Code	IK08

Features

Dimensions	Width: 180 mm Height: 110 mm Depth: 90 mm
Cable entry (quantity x diameter)	M20 M20/M25 M32/M40
No. of metric knockouts	16 x M20 2 x M20/M25 2 x M32/M40
Operating temperature range	-35 °C...80 °C
Basic material	Polycarbonate
Packs of	2 pc(s).
Net weight	0,77 kg
Gross weight	0,863 kg
Customs tariff number	84879090
ETIM 9	EC000261
ECLASS 8.0	27180101
Product description	PK Polycarbonate enclosure, WHD: 180x110x90 mm, fibreglass-reinforced polycarbonate, with knockouts, with grey cover

Approvals

Approvals	C-UL DNV UL
Explanations	Declaration of conformity

Tender text

Polycarbonat-Gehäuse mit Vorprägungen

Polycarbonate enclosure with solid cover with knockouts

Enclosure: Fibreglass-reinforced polycarbonate
with knockouts for cable entry

Cover: Fibreglass-reinforced polycarbonate
all-round foamed-in PU seal

Cover screws: Polyamide

Insulating bungs: Polyethylene

Supply includes: Cover screws

Insulating bungs for wall mounting screws

Accessories: Wall mounting bracket

Protection category to IEC 60 529: IP 66

Protection category NEMA: NEMA 4X

Colour: similar to RAL 7035

Dimensions (W x H x T): 180 x 110 x 90 mm