

Rittal – The System.

Faster – better – everywhere.



SV 9612.000

**Mini-PLS busbar connection
adaptor**

State: 04.07.2026. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9612.000 - Mini-PLS busbar connection adaptor

Rated current 63 A/1600 A/250 A, cable outlet top/bottom

Features

Model No.	SV 9612.000
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035 Chassis: RAL 9011
Clamping area for laminated copper bars (W x H)	17 x 15 mm
Note	Wire end ferrules should be used with fine wire conductors
Cable outlet	Top/bottom
Rated operating voltage	690 V
Rated current max.	250 A
Dimensions	Width: 115 mm Height: 182 mm
Connection of round conductors	10 - 120 mm ²
Packs of	1 pc(s).
Net weight	0,88 kg
Gross weight	1,096 kg
Copper weight (kg per piece)	0,3
Customs tariff number	85369010
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV Mini-PLS busbar connection adaptor, 250 A, 690 V, 3-pole, round conductor connection 10-120 mm ² , clamping area WH: 17x15 mm

Approvals

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK
