

# Rittal – The System.

Faster – better – everywhere.



## SV 9614.100

## Mini-PLS component adaptor

State: 01.05.2026. (Source: [rittal.com/hr-hr](http://rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9614.100 - Mini-PLS component adaptor

Maximum rated current from 12 A to 100 A.

## Features

|                             |   |
|-----------------------------|---|
| Model No.                   | SV 9614.100   |
| Material                    | Polyamide<br>Fire protection corresponding to UL 94-V0  |
| Colour                      | RAL 7035  |
| Connection cables (AWG)     | AWG 12  |
| Rated operating voltage     | 690 V, 3~   |
| Rated current max.          | 25 A  |
| Dimensions                  | Width: 45 mm<br>Height: 160 mm  |
| Support rails Qty/height    | 1 / 7.5 mm  |
| To fit manufacturer (model) | ABB<br>Eaton<br>Schneider Electric<br>Siemens<br>MS116<br>PKZM0 bis 25 A<br>PKZM01 bis 25 A<br>PKE12<br>PKE32 bis 25 A<br>GV2-P bis 25 A<br>GV2-RT<br>GV2-LE10<br>GV3 bis 25 A<br>3RV10 21<br>3RV20 21 bis 25 A<br>3RV10 11<br>3RV20 11 |
| Packs of                    | 1 pc(s).  |
| Net weight                  | 0,25 kg   |

# Features

---

|                              |  |
|------------------------------|--|
| Gross weight                 | 0,29 kg  |
| Copper weight (kg per piece) | 0,041  |
| Customs tariff number        | 85369095   |
| ETIM 9                       | EC001531   |
| ECLASS 8.0                   | 27370304   |
| Product description          | SV Mini-PLS component adaptor, 25 A, 690 V, 3-pole, connection cable AWG 12, WH: 45x160 mm, support rail H: 7,5 mm |

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | UR + C-UR (recognized)                                    |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |