

Rittal – The System.

Faster – better – everywhere.



SV 9616.000

Mini-PLS component adaptor

State: 03.06.2026. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9616.000 - Mini-PLS component adaptor

Maximum rated current from 12 A to 100 A.

Features

Model No.	SV 9616.000
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Connection cables (AWG)	AWG 10
Rated operating voltage	690 V, 3~
Rated current max.	40 A
Dimensions	Width: 54 mm Height: 160 mm
Support rails Qty/height	1 / 7.5 mm
To fit manufacturer (model)	Schneider Electric Siemens GV3 max. 40 A 3RV10 31 max. 40 A
Packs of	1 pc(s).
Net weight	0,27 kg
Gross weight	0,32 kg
Copper weight (kg per piece)	0,046
Customs tariff number	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV Mini-PLS component adaptor, 40 A, 690 V, 3-pole, connection cable AWG 10, WH: 54x160 mm, support rail H: 7,5 mm

Approvals

Approvals

UR + C-UR (recognized)

Explanations

Declaration of conformity

Declaration of conformity UK