## Rittal – The System.

Faster - better - everywhere.





# SV 9635.320 Component adaptor

State: 02.11.2025. (Source: rittal.com/hr-hr)



# SV 9635.320 - Component adaptor 3-pole

For assembly of switchgear and protective gear.

#### **Features**

Model No.	SV 9635.320
Design	Basic
Function principle	For mechanical attachment and direct contacting of electrical equipment on the board
Material	Polyamide Fire protection corresponding to UL 94
Colour	RAL 7035
Note	The technical data may vary for UL applications
Rated current max.	32 A
Rated operating voltage	600 V (DC), 3~ 690 V (AC), 3~
Number of poles	3-pole
Electrical ratings UL	Rated operating voltage (max.) UL: 600 V AC
Connection cables (AWG)	AWG 10
Length of connection cable	100 mm
Support rails Qty/height	1 / 10 mm
Support rail type	static
Dimensions	Width: 45 mm Height: 160 mm Depth: 34.5 mm
Packs of	4 pc(s).
Net weight	0.44
Gross weight	0.513
Copper weight (kg per piece)	0.044

© Rittal 2025

### Features

Customs tariff number	85369095
EAN	4028177817364
ETIM 9	EC001531
ECLASS 8.0	27370304

## **Approvals**

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3