

Rittal – The System.

Faster – better – everywhere.



SV 9677.905 Connection adaptor

State: 04.06.2026. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.905 - Connection adaptor

For the connection of round conductors. For bar systems with 185 mm centre-to-centre spacing.

Features

| | |
|---|--|
| Model No. | SV 9677.905 |
| Material | Chassis: Fibreglass-reinforced polyester Fire protection corresponding to UL 94-V0 |
| Colour | RAL 7035 |
| Supply includes | Contact hazard protection cover plate |
| For bar systems with centre-to-centre spacing | 185 mm |
| Cable outlet | Top/bottom |
| Type of electrical connection | Screw M12 |
| Number of poles | 3-pole |
| Rated current max. | 1.400 A |
| Rated operating voltage | 690 V, 3~ |
| Note | When using components on busbars with contact hazard protection cover, the contact terminal must be used |
| Dimensions | Width: 100 mm Height: 960 mm |
| Connection of round conductors | 6 - 300 mm ² |
| To fit busbars | Height: 10 mm |
| Packs of | 1 pc(s). |
| Net weight | 11 kg |
| Gross weight | 11,5 kg |
| Copper weight (kg per piece) | 4,41 |
| Customs tariff number | 85369010 |
| ETIM 9 | EC001531 |

Features

| | |
|---------------------|---|
| ECLASS 8.0 | 27370304 |
| Product description | SV Connection adaptor, 1400 A, 690 V, 3-pole, 185 mm, cable outlet bottom, round conductor connection 6-300 mm ² |

Approvals

| | |
|--------------|---|
| Explanations | Declaration of conformity Declaration of conformity UK |
|--------------|---|