

Rittal – The System.

Faster – better – everywhere.



KL 1529.510 Terminal boxes KL

State: 12/05/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KL 1529.510 - Terminal boxes KL without gland plate

Spray-finished enclosure with sheet steel cover, without gland plate Protection category IP 66.

Features

| | |
|-----------------------------------|--|
| Model No. | KL 1529.510 |
| Material | Enclosure: Sheet steel Cover: Sheet steel, all-round foamed-in PU seal |
| Surface finish | Enclosure and cover: Dipcoat primed, powder-coated on the outside, textured paint |
| Colour | RAL 7035 |
| Supply includes | Enclosure with cover Quick-release fastener including plastic bushes |
| Protection category NEMA | NEMA 4 |
| Protection category to IEC 60 529 | IP 66 |
| IK Code | IK08 |
| Dimensions | Width: 200 mm Height: 150 mm Depth: 120 mm |
| Material thickness - cover | 1.25 mm |
| Material thickness - enclosure | 1.25 mm |
| Basic material | Sheet steel |
| Packs of | 1 pc(s). |
| Net weight | 1.58 kg |
| Gross weight | 1.77 kg |
| Customs tariff number | 73269098 |
| ECLASS 8.0 | 27180101 |
| Product description | KL Terminal box, WHD: 200x150x120 mm, Sheet steel, without mounting plate, with cover, without gland plate |

Approvals

Approvals

Bureau Veritas
DNV
Lloyds Register
UL + C-UL (listed)

Explanations

Manufacturer's declaration
Declaration of conformity UK