## Rittal - The System.

Faster - better - everywhere.





EB 1554.500 E-Box EB

State: 6/11/2025 (Source: rittal.com/ie-en)



## EB 1554.500 - E-Box EB

Wall-mounted enclosure with door and mounting plate of sheet steel. Protection category IP 66. With 180° hinge. Lock insert may also be exchanged for individual lock systems.

## **Features**

| Model No.                            | EB 1554.500  |
|--------------------------------------|--|
| Material                             | Enclosure and door: Sheet steel, all-round foamed-in PU seal   |
| Surface finish                       | Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting plate: Zinc-plated |
| Colour                               | RAL 7035   |
| Supply includes                      | Enclosure with hinged door 180° hinge Cam lock with 3 mm double-bit insert Mounting plate                    |
| Protection category NEMA             | NEMA 4   |
| Protection category to IEC 60 529    | IP 66  |
| IK Code                              | IK08   |
| Dimensions                           | Width: 200 mm<br>Height: 300 mm<br>Depth: 120 mm   |
| Dimensions mounting plate (W x H)    | 175 mm x 285 mm  |
| Material thickness - enclosure       | 1.25 mm  |
| Material thickness - door            | 1.25 mm  |
| Material thickness of mounting plate | 2 mm   |
| Lock                                 | Lock version: Cam<br>Number of locks: 1<br>Lock insert: 3 mm double-bit                                      |
| Basic material                       | Sheet steel  |

© Rittal 2025

2

## Features

| Packs of              | 1 pc(s).      |
|-----------------------|---------------|
| Net weight            | 3.361         |
| Gross weight          | 3.561         |
| Customs tariff number | 94032080      |
| EAN                   | 4028177251724 |
| E-Number Sweden       | E3404649      |
| ECLASS 8.0            | 27180101      |

# **Approvals**

| Approvals    | Bureau Veritas               |
|--------------|------------------------------|
|              | C-UL                         |
|              | Lloyds Register of Shipping  |
|              | UL                           |
|              | UL + C-UL (listed)           |
| Explanations | Manufacturer's declaration   |
|              | Declaration of conformity    |
|              | Declaration of conformity UK |
|              |                              |

© Rittal 2025 3

### Tender text

E Box, protection category IP 66 Enclosure:

sturdy sheet steel construction, of 1.38 mm sheet steel, folded and welded from a single piece, with all-round protection channel on the door aperture, with recessed holes for wall mounting brackets in the rear panel.

#### Doors:

1.5 mm - 2 mm sheet steel, sealed, with foamed-in seal and screw-fastened hinges, 180° opening angle, cam lock with double-bit insert to DIN 43668.

### Mounting plate:

2 or 2.5 mm sheet steel, zinc-plated

#### Accessories:

Lock systems, wall mounting brackets, earth straps

#### Surface finish:

Steel is cleaned, degreased, phosphated, electrophoretic dipcoat-primed and polyester powder-coated in textured RAL 7035, pale grey.

Dimensions (W x H x D): 200 x 300 x 120 mm

© Rittal 2025 4