

Rittal – The System.

Faster – better – everywhere.



SZ 1581.100

Metal gland plate

State: 24/08/2025 (Source: [rittal.com/ie-en](https://www.rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 1581.100 - Metal gland plate with metric knockouts

Simply knock out the holes for the cable glands using a screwdriver, IP 66 when mounting in the usual position at the bottom.

Features

| | |
|-----------------------------------|---|
| Model No. | SZ 1581.100 |
| Product description | Simply knock out the holes for the cable glands using a screwdriver. |
| Material | Sheet steel |
| Colour | RAL 7035 |
| Note | The allocation of gland plate sizes is indicated on the relevant enclosures |
| No. of metric knockouts | 12 x M20 |
| Dimensions | Width: 221 mm Depth: 90 mm |
| To fit | Enclosure type: KL |
| Gland plate | Size: 2 |
| Protection category to IEC 60 529 | IP 66 when mounting in the usual position at the bottom |
| Number knockouts | 12 |
| Metric diameter | M20 |
| Packs of | 1 pc(s). |
| Net weight | 0.23 |
| Gross weight | 0.25 |
| Customs tariff number | 73079100 |
| EAN | 4028177390843 |
| E-Number Sweden | E3404794 |
| ETIM 9 | EC000211 |
| ETIM 8 | EC000211 |

Features

ECLASS 8.0

27142421