

Rittal – The System.

Faster – better – everywhere.



AX 2503.020

Wall mounting bracket

State: 28/06/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2503.020 - Wall mounting bracket for AX sheet steel, KX sheet steel, AX IT, EL

Ideal for convenient one-person assembly of wall-mounted enclosures, even in confined spaces.



Features

| | |
|---------------------|--|
| Model No. | AX 2503.020 |
| Product description | Ideal for convenient one-person assembly of wall-mounted enclosures, even in confined spaces. |
| Benefits | <p>Screw-fastened directly from the rear with a self-tapping screw into the enclosure eyelet</p> <p>Simply suspend the wall-mounted bracket from a screw in the wall</p> <p>Different mounting positions allow the wall mounting bracket to be tailored to local conditions on site.</p> <p>As an alternative to the self-tapping screw, the support may also be secured from the inside using a screw and nut</p> <p>Additional option of attaching with a nut for dynamic applications</p> |
| Material | Sheet steel, zinc-plated |
| Supply includes | Wall mounting bracket Cover cap Assembly parts |
| Wall distance | 40 mm |
| To fit | Enclosure type: AX sheet steel KX sheet steel AX IT EL AX wall-mounted enclosure, 3-part |

Features

| | |
|-------------------------------|--|
| Type rating to UL 50E | Type 1 Type 3R Type 4 Type 12 |
| Packs of | 4 pc(s). |
| Net weight | 0.56 kg |
| Gross weight | 0.568 kg |
| PCF per pack (cradle-to-gate) | 2.2 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 83025000 |
| ETIM 9 | EC002625 |
| ETIM 8 | EC002625 |
| ECLASS 8.0 | 27189234 |
| Product description | SZ Wall mounting bracket, for AX and KX, sheet steel, wall distance: 40 mm |

Approvals

| | |
|-----------|-------------------------|
| Approvals | DNV UL + C-UL - FTTA |
|-----------|-------------------------|