

# Rittal – The System.

Faster – better – everywhere.



## SZ 2560.400 Metal gland plate

State: 26/06/2026 (Source: [rittal.com/ie-en](http://rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2560.400 - Metal gland plate

As spare/replacement part for the standard gland plates supplied loose, IP 66 when mounting in the usual position at the bottom.

## Features

|                                   |   |
|-----------------------------------|---|
| Model No.                         | SZ 2560.400   |
| Design                            | solid   |
| Product description               | As spare/replacement part for the standard gland plates supplied loose.     |
| Material                          | Sheet steel   |
| Colour                            | RAL 7035  |
| Note                              | The allocation of gland plate sizes is indicated on the relevant enclosures |
| Dimensions                        | Width: 160 mm<br>Depth: 70 mm   |
| To fit                            | Enclosure type: AE  |
| Gland plate                       | Size: 1   |
| Protection category to IEC 60 529 | IP 66 when mounting in the usual position at the bottom                     |
| Packs of                          | 1 pc(s).  |
| Net weight                        | 0.119 kg  |
| Gross weight                      | 0.128 kg  |
| Customs tariff number             | 73079100  |
| ETIM 9                            | EC000211  |
| ETIM 8                            | EC000211  |
| ECLASS 8.0                        | 27142421  |
| Product description               | SZ Metal gland plate, closed, WD: 160x70 mm, size: 1                        |