


**Rittal – The System.**

Faster – better – everywhere.



**SZ 2561.500**

**Plastic cable gland plates**

State: 1/09/2025 (Source: [rittal.com/ie-en](http://rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2561.500 - Plastic cable gland plates with membranes

Simply pierce the plastic and pull through the cable, protection category IP 65 with careful cable entry.

## Features

Model No.	SZ 2561.500
Product description	Simply pierce the plastic with a sharp object, and pull through the cable.
Material	Plastic to UL 94-V0 Halogen free
Colour	Similar to RAL 7035
Note	The allocation of gland plate sizes is indicated on the relevant enclosures
Dimensions	Width: 330 mm Depth: 90 mm
To fit	Enclosure type: AE
Gland plate	Size: 3
Protection category to IEC 60 529	IP 65
No. of cable entries and Ø (mm) min.-max.	17 x 6-11 27 x 10-15 2 x 15-21 4 x 16-25 2 x 19-34
Packs of	1 pc(s).
Net weight	0.365
Gross weight	0.37
Customs tariff number	39269097
EAN	4028177325593
E-Number Sweden	E3404727

# Features

ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421