


# Rittal – The System.

Faster – better – everywhere.



## AX 2571.100 Metal gland plate

State: 13/07/2025 (Source: [rittal.com/ie-en](https://www.rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AX 2571.100 - Metal gland plate with metric knockouts, for AX

Simply knock out the holes for the cable glands using a screwdriver.

## Features

Model No.	AX 2571.100
Product description	Simply knock out the holes for the cable glands using a screwdriver.
Material	Sheet steel
Colour	RAL 7035
Note	The allocation of gland plate sizes is indicated on the relevant enclosures
No. of metric knockouts	2 x M12 2 x M16 9 x M20 5 x M25 1 x M32 1 x M40
Dimensions	Width: 256 mm Depth: 149 mm
To fit	Enclosure type: AX
Gland plate	Size: 1
Protection category to IEC 60 529	IP 66 if installed correctly
Type rating to UL 50E	Type 1 Type 12K
Number knockouts	2 2 9 5 1 1

# Features

Metric diameter	M12
	M16
	M20
	M25
	M32
	M40
Packs of	1 pc(s).
Net weight	0.46
Gross weight	0.469
PCF per pack (cradle-to-gate)	2.3 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
EAN	4028177925304
E-Number Sweden	E3465295
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421

# Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------