



# AX 2572.100 - Metal gland plate with metric knockouts, for AX

Simply knock out the holes for the cable glands using a screwdriver.

## Features

|                                   |  |
|-----------------------------------|--|
| Model No.                         | AX 2572.100  |
| Product description               | Simply knock out the holes for the cable glands using a screwdriver.   |
| Material                          | Sheet steel  |
| Colour                            | RAL 7035   |
| Note                              | The allocation of gland plate sizes is indicated on the relevant enclosures                                    |
| No. of metric knockouts           | 6 x M16<br>4 x M20<br>10 x M25<br>2 x M32<br>2 x M40   |
| Dimensions                        | Width: 339 mm<br>Depth: 149 mm   |
| To fit                            | Enclosure type: AX   |
| Gland plate                       | Size: 2  |
| Protection category to IEC 60 529 | IP 66 if installed correctly   |
| Type rating to UL 50E             | Type 1<br>Type 12K   |
| Packs of                          | 1 pc(s).   |
| Net weight                        | 0.6 kg   |
| Gross weight                      | 0.605 kg   |
| PCF per pack (cradle-to-gate)     | 3 kg CO2 eq (Cat B)  |
| Note on PCF category              | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |

# Features

---

|                       |  |
|-----------------------|--|
| Customs tariff number | 73079100   |
| ETIM 9                | EC000211   |
| ETIM 8                | EC000211   |
| ECLASS 8.0            | 27142421   |
| Product description   | SZ Metal gland plate, for AX, with metric knockouts, WD: 339x149 mm, for gland plates size 2 |

# Approvals

---

|           |                  |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|