

Rittal – The System.

Faster – better – everywhere.



FT 2763.010

Viewing window

State: 17/08/2025 (Source: [rittal.com/ie-en](https://www.rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



FT 2763.010 - Viewing window for AX

For external mounting on AX enclosures instead of a door and on surfaces.



Features

Model No.	FT 2763.010
Design	60 section
Product description	For external mounting on AX enclosures instead of a door and on surfaces.
Material	Frame: Aluminium, natural anodised. Glass panel: Acrylic
Supply includes	Plastic handle with lock insert no. 3524 E
Protection category to IEC 60 529	IP 54
To fit Model No.	1050.000 1350.000 1007.000
To fit	Enclosure type: AX Width: = 500 mm Height: = 500 mm
Dimensions	Width: 497 mm Height: 497 mm Depth: 62 mm
Visible area	Viewing window width: 437 mm Viewing window height: 437 mm

Features

Build depth for components (max.)	58 mm
Packs of	1 pc(s).
Net weight	3.44
Gross weight	3.46
Customs tariff number	76101000
EAN	4028177938601
ETIM 9	EC002527
ETIM 8	EC002527
ECLASS 8.0	27182204